






Notes

- 1. Maximum operating angle is 10° at higher speeds
- 2. Maximum operating angle is 30° at lower speeds.
- 3. Lubrication is required at all times. Use vacuum compatible lubricant if used inside vacuum chamber.

Rev	Description	Date
A	Initial Release	



2x Spot Drill

2-56 Set Screws Included



Accu-Glass Products Inc.
 25047 Anza Drive
 Valencia, CA 91355
 T 818-365-4215
 F 818-365-7074
 www.accuglassproducts.com

UNCONTROLLED WEB DRAWING

Proprietary and Confidential
 The information contained in this drawing is the sole property of Accu-Glass, Products Inc. Any reproduction, in part or as whole, without the written permission of Accu-Glass Products, Inc., is strictly prohibited.

Material Stainless Steel, 303	
Tolerances, unless otherwise specified	
.X ± .030	Angles ± 0.5° Finish 63Ra
.XX ± .010	
.XXX ± .005	

Title Universal Joint, .125 Shaft Dia.			
Drawn by Date	Ligeti 8/6/2014	No. 112536	Rev. A
Approved			Sheet